

Item no.: 3203420



TOOLCRAFT

Data Sheet



Tension dial



Tension indicator



Tightening

Automatic Nylon Cable Tie Tensioner

Innovative, Automatic trim, Adjustable tension, Flush cut

- Tightens on nylon cable tie with faster and securer.
- Features rugged metal/ rubber construction with durability.
- Adjustable 8-level bundling pressure provides accurate setting.
- Automatic cut-off excess tie when pull force is reached.
- Eliminates sharp edges on cable tie without damage objects.
- Tethering hole for multi-use and convenient storage.
- Greater comfort ergonomic grooved grips reduce hand fatigue.

Description	Length	Weight
For cable tie size width from 2.5 to 4.8mm, thickness up to 1.6mm.	172mm(6.8")	280g

Tensile Strength:

Strength Level	Tensile Strength
0	3 Kgf
3	5 Kgf
5	8 Kgf
8	11 Kgf

*For reference only

Packing:

Packaging	Master Carton (PCS)	N.W.	G.W.	CUFT	Carton Dimensions (mm)
		(KGS)	(KGS)	(MEAS)	
Plain Box	40	14	15	1.7	420 x 300 x 400