


Data Sheet

CAM switch

Version 06/24



	LW40-20 C02/1C48I	
	OFF	ON
	270°	0°
1 — 2		×
3 — 4		×

Data Sheet

Specification

Switch rating

U _i	I _{th}	U _e	AC-23A	AC-3	DC-21A
			I _e	I _e	I _e
690V	20A	AC 440V	15A	11A	
		DC 240V			0.4A
		DC 120V			1A

Mechanical life

Without load: 8500 times; with load: 1500 times; the total number of operating cycles is 10,000 times

Working conditions

1. -5 °C~ 40 °C, and the average temperature within 24 hours does not exceed 35 °C.
2. Should not be installed above 2000m above sea level.
3. The humidity should not exceed 50% when the ambient temperature is 40 °C and higher humidity is allowed for lower temperature, for example, it can reach 90% at 20 °C