

4G mini camera

FEATURE

Image Sensor

- Sensor: 1/2.9" full color 2MP HD CMOS sensor
- Lens: 2MP F2.0
- PT Angle: D: 130° (wide angle), H: 117° , V: 60.5°
- Minimum Illumination: 0.01 Lux
- Lens Mount: 10mm
- Day & Night: 6 x 950nm, 14mil infrared light
- DNR and WDR: Supported
- Night Vision Distance: 8 to 10 meters

Video & Audio

Max. Resolution: 1920*1080

Frame Rate: 15fps

Video Compression: H.265

H.265 Type: Supported

Video and Audio Bit Rate: automatically adaptive

Max. Bit rate: 2Mbps

Network

- Frequency Range:
 - LTE FDD: B1/B3/B8
 - LTE TDD: B34/B38/B39/B40/B41
 - WCDMA: B1/B8"
- Channel Bandwidth: 10 to 100 M bps
- Transmission Rate: 12.5 M bps
- Protocol: Support TCP/IP, HTTP, UDP, RTP , RTSP, DNS, DDNS, DHCP, FTP
- Wired Network: NOT supported

Storage

- Local Storage: Micro SD card (up to 128G) in FAT32

format

- Cloud Storage: Supported

Function

- Smart Alarm: Radar motion detection (can work through a window)
- Customized Alert Area: Supported
- Two-way Talk: NOT supported
- General Function: live view, Recording length setting, image flip and rotation, time synchronization
- Recording modes: motion detection (default), fulltime recording, manual recording

TECHNICAL SPECIFICATIONS

- Operating Conditions:
 - working temp (-10°C~70°C)
 - storage temp (-20°C~75°C) "
- Power Supply: DC 5V / 2A
- Power Consumption: 10W
- Product Size: 54*38*42mm
- Product Net weight: 210g
- Product Gross weight: 88g
- Color: Black

LOGISTICS

- Gift box Size (w*h*d): 144.5*89.4*45.6mm
- Outer carton Size (w*h*d): 40*30*48cm
- PCS: 100pcs
- Gross Weight: 22.5kg

NOTE: This product works on 5VDC, so use a power bank/battery that works on 5VDC and not 12VDC!

