


Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2013 with regard to energy labelling of electronic displays

	Parameter	Parameter or value and precision			Unit
1.	Supplier's name or trademark.	Denver			
	Supplier's address.	Denver A/S, Omega, Soeften 5A, 8382 Hinnerup, DK			
2.	Model identifier	PFF-1012W			
3.	Energy Efficiency Class for Standard Dynamic Range (SDR)	C			
4.	On mode power demand in SDR	5,4			W
5.	Energy Efficiency Class for High Dynamic Range (HDR)	n.a.			
6.	On mode power demand in HDR, if implemented	n.a.			W
7.	Off mode, power demand, if applicable	0,1			W
8.	Standby mode power demand, if applicable	0,1			W
9.	Networked standby mode power demand, if applicable	1,3			W
10.	Electronic display category	Other			
11.	Size ratio	16	:	9	
12.	Screen resolution	1 280	x	800	pixels
13.	Screen diagonal	25,5			cm
14.	Screen diagonal	10			inches
15.	Visible screen area	2,9			dm ²
16.	Panel technology used	LED LCD			
17.	Automatic Brightness Control (ABC) available	No			
18.	Voice recognition sensor available	No			
19.	Room presence sensor available	No			
20.	Image refresh frequency rate (default)	60			Hz
21.	Minimum guaranteed availability of software and firmware updates (from the date of end of the placement on the market)	-			Years
22.	Minimum guaranteed availability of spare parts (from the date of end of the placement on the market)	-			Years
23.	Minimum guaranteed product support	-			Years
	Minimum duration of the general guarantee offered by the supplier	-			Years
24.	Power supply type	External			
25.	External power supply (non standardized and included in the product box)				
	<i>i</i>	-			
	<i>ii</i>	Input voltage	-		V

	<i>iii</i>	Output voltage	-	V
26.	External standardised power supply (or suitable one if not included in the product box)			
	<i>i</i>	-		
	<i>ii</i>	Required output voltage	-	V
	<i>iii</i>	Required delivered current (minimum)	-	A
	<i>iv</i>	Required current frequency	-	Hz

Model placed on the Union market from 01/04/2024



EPREL registration number: 1957870

<https://eprel.ec.europa.eu/qr/1957870>

Supplier: Denver A/S (Importer)

Website: www.denver.eu

Customer care service:

Name: Denver A/S

Website: www.denver.eu

Email: contact.hq@denver.eu

Phone: +4586226100

Address:

Omega, Soeften 5A
8382 Hinnerup
Denmark