





POLYCARBONATE
VERSION ONLY
c  US LISTED
FILE #E65324
TYPE 4,4X,6,6P



Dimensions:
mm
[inches]

Enclosures can be Factory Modified (Milling, Drilling, Printing etc.)
Contact Factory (modshop@hammfg.com) for quotes
Solid models of this enclosure available in .stp or .x_t
(Part number and text placement/orientation on our products are subject to change,
we do not recommend using them as a locating reference for modification purposes)

NOTE

Purchased assembly includes styled box, flanged lid, 2 cover screws, and preformed silicone gasket.

General Purpose ABS version is not UL approved. (Matl UL94 - HB)

Polycarbonate version is UL 508 approved. (Matl UL94 - 5VA @ 3mm)

Recommended Cover screw torque -- 85-92 ozf-in (60-65 cN-m)

1555AF	
1555AF Regular Enclosure	
General Purpose ABS RAL-7035	1555AF22GY
Polycarbonate RAL-7035	1555A2F22GY
ACCESSORIES	
Steel Inner Panels	1555AFPL
Silicone Pre-formed Gasket Black (Pkg 2)	1554AGASKET
Steel Panel / P.C. Board Self Tapping Screw [#4 X 1/4" (6.4mm) Plated]	1555TS100
Stainless Steel Cover Screws [M4-0.7 X 20mm] (Pkg 50)	SC576-50



HAMMOND.

1555AF22

www.hammondmfq.com