



2-speed cordless combi drill

With brushless motor and QuickIN interface. Perfectly suited to drilling up to 13 mm in metal, stone and masonry.

Part number: 7 104 07 62 00 0

FEIN benefits

- > 2-speed solid metal gearbox and switchable striking mechanism for optimum drilling in metal, stone and masonry.
- > Enjoy the greatest versatility with the FEIN QuickIN system. Work at speed in metal and timber with just one tool.
- > QuickIN solid metal drill chuck (120 Nm) with carbide-tipped clamping jaws and high clamping forces.
- > Brushless FEIN PowerDrive motor with 30 % higher efficiency and long service life.
- > Mechanical torque setting.
- > Compact design.
- > The AMPShare interface makes almost 50% more screw connections (approx. 1300 screw connections, diameter of 5 x 40 mm in timber) possible per battery charge with the same level of FEIN quality. (ProCORE 4 Ah).
- > Bit and belt holder on the side for ergonomic and flexible handling.
- > Compatible with all 18 V AMPShare ProCORE batteries and chargers for even more power and flexibility. Also suitable for 18 V Bosch Professional cordless devices.
- > Compatible with Bosch Professional 18 V batteries (available since 2008) and AMPShare batteries.
- > Maximum work progress with AMPShare 18V ProCORE batteries: COOLPACK 2.0 technology delivers a 135% longer battery life. State-of-the-art cell technology and intelligent battery management deliver 87% more power than with conventional batteries. "Electronic Cell Protection" (ECP) protects the battery from overload, overheating and total discharge.
- > Ideally equipped for every form of use. Mobile working with the L-BOXX system.

Supplied

- | | | |
|----------------------------------|--|----------------------------------|
| ✓ 1 QuickIN drill chuck (120 Nm) | ✓ 1 belt clip | ✓ 1 magnetic bit storage |
| ✓ 1 tool case (L-Boxx 136) | ✓ 2 Li-Ion storage battery GBA 28V 5.0 Ah AS (92604346020) | ✓ 1 rapid charger GAL 1880 CV AS |

Features

- | | | |
|-------------------------|-------------------------------------|--------------------------------|
| ✓ Removable drill chuck | ✓ aus_QuickIN_Zubehör_Schnittstelle | ✓ aus_zuschaltbares_Schlagwerk |
|-------------------------|-------------------------------------|--------------------------------|



Technical data

GENERAL TECHNICAL DATA

Battery voltage	18 V
Battery capacity	5 Ah
Battery compatibility	Li-ion / ProCORE Li-ion
Battery interface	18 V AMPShare
Motor	brushless
Gearbox	2-speed
Accessory interface	QuickIN
Speed, no load	450 / 2,000 rpm
Impacts	7,360 / 32,000 rpm
Max. torque (hard/soft)	60 / 38 Nm
Torque levels	22 + 1
Drill chuck clamping width	1.5 - 13 mm
Fastening	8 x 300 mm
Capacity in steel Ø	13 mm
Capacity in wood Ø	50 mm
Capacity in stone Ø	13 mm
Tapping	M 10
Weight without storage battery	1.50 kg

VIBRATION AND NOISE EMISSION VALUES

Sound pressure level LpA	92,9 dB
Uncertainty of measured value KpA	3 dB
Sound power level LWA	100,9 dB
Uncertainty of measured value KWA	3 dB
Sound peak value LpCpeak	110,0 dB
Uncertainty of measured value KpCpeak	3 dB
Vibration value 1 ahv 3-way	ah,D 1,4 m/s ²
Vibration value 2 ahv 3-way	ah 0,6 m/s ²
Uncertainty of measured value Ka	1,5 m/s ²

Examples of use



**Kompatibel mit
AMPSHare-/ Bosch
Professional 18 V
Akkus.** | Compatible
with AMPSHare/Bosch

Professional 18 V batteries. | Compatible avec
les batteries 18 V AMPSHare/Bosch Professional. |
Compatible con baterías AMPSHare/Bosch
Professional de 18 V. | Compatibile con le batterie
AMPSHare / Bosch Professional da 18 V.

