



ASCD 18-300 W2 AS Ready to-use-top Set

User set contains a cordless impact wrench/driver

Cordless impact wrench/driver with 1/2" square head tool mounting. The user set includes 3-part set of impact sockets (17 / 19 / 21 mm) and circlip along with a battery (GBA 18 V 5.0 Ah AS) and rapid charger (GAL 1880 CV AS).

Part number: 7 115 10 62 00 0

FEIN benefits

- > For extreme precision work: The ASCD 18-300 W2 AS with electronic torque setting (6 levels) prevents screw heads from shearing off.
- > Be ready to go instantly with tool and appropriate accessories for driving metric screws.
- > 3-part set of impact sockets with appropriate circlip for widths across flats of 17 mm, 19 mm and 21 mm.
- > VARIO 1/2" adapter, available as an extra and developed by FEIN, suitable for all VARIO accessories for simple and mechanical drilling, countersinking, tapping, recutting and cleaning of through holes up to a maximum of M18. Turns the impact wrench/driver into a tapper, thereby adding a whole new tool to the range of applications.
- > Brushless FEIN PowerDrive motor with 30 % higher efficiency and long service life.
- > 1/2" square for holding sockets.
- > Metric screws up to M18 (8.8).
- > 10% more torque in reverse running to loosen screws which are extremely tight.
- > Robust solid metal impact gear.
- > Contact guard on gearbox head.
- > Up to 600 screw connections (M18) with one battery charge (ProCORE 4 Ah).
- > Compact design.
- > Bit and belt holder on the side for ergonomic and flexible handling.
- > Compatible with Bosch Professional 18 V batteries (available since 2008) and AMPShare batteries.
- > Maximum work progress with AMPShare 18V storage batteries: COOLPACK 1.0 technology ensures a longer storage battery life compared with batteries without COOLPACK technology and therefore makes longer operating periods possible. ECP protects the storage battery against overload, overheating and total discharge.
- > Ideally equipped for every form of use. Mobile working with the L-BOXX system.

Supplied

- | | | |
|---|-------------------------------------|----------------------------------|
| ✓ 1 x ASCD 18-300 W2 AS (including belt clip, bit holder) | ✓ 2 BATTERY PACK GBA 18 V 4.0 AH AS | ✓ 1 rapid charger GAL 1880 CV AS |
| ✓ 1 x set of impact sockets | ✓ 1 x locking spring | ✓ 1 tool case (L-Boxx 136) |

Technical data

GENERAL TECHNICAL DATA

Battery voltage	18 V
Battery compatibility	Li-ion / ProCORE Li-ion
Battery interface	18 V AMPShare
Motor	brushless
Speed, no load	0 - 1700 rpm
Impacts	0 - 3400 rpm
Max. torque	290 Nm
Torque levels	6
Tool Holder	1/2 in Outer square
Max. metric screw	M18 (8.8)
Wood screw Ø	8 x 300 mm
Weight without storage battery	1.20 kg

VIBRATION AND NOISE EMISSION VALUES

Sound pressure level LpA	99,2 dB
Uncertainty of measured value KpA	3 dB
Sound power level LWA	107,2 dB
Uncertainty of measured value KWA	3 dB
Sound peak value LpCpeak	121,5 dB
Uncertainty of measured value KpCpeak	3 dB
Vibration value 1 ahv 3-way	ah 15,0 m/s ²
Uncertainty of measured value Kα	1,5 m/s ²

Examples of use



**Kompatibel mit
AMPShare-/ Bosch
Professional 18 V
Akkus.** | Compatible
with AMPShare/Bosch

Professional 18 V batteries. | Compatible avec
les batteries 18 V AMPShare/Bosch Professional. |
Compatible con baterías AMPShare/Bosch
Professional de 18 V. | Compatibile con le batterie
AMPShare / Bosch Professional da 18 V.

