



ABH 18-26 AS

Cordless rotary hammer drill

With SDS plus and an impact energy of 2.6 joules for drilling up to 26 mm in concrete.

Part number: 7 140 03 62 00 0

FEIN benefits

- > The powerful, brushless motor delivers 2.6 joules of impact energy and ensures rapid drilling progress as well as high chisel grinding capacity.
- > Kickback monitoring with intelligent rapid shutdown should the hammer drill kick back suddenly for optimum user protection.
- > Electronic Precision Control (EPC) slowly ramps up the working speed for perfect handling and control when working with sensitive materials and challenging surfaces.
- > Simple and precise speed control using the throttle.
- > Fatigue-free working thanks to compact design and few vibrations.
- > Change the chisel position (Vario-Lock) – lock the chisel in 36 positions for the optimum working position every time.
- > Bright working area thanks to integrated LED light.
- > Clamps or hooks the bit if the drive to the drill spindle is interrupted.
- > Compatible with Bosch Professional 18 V batteries (available since 2008) and AMPShare batteries.
- > Maximum work progress with AMPShare 18V ProCORE batteries: COOLPACK 2.0 technology delivers a 135% longer battery life. State-of-the-art cell technology and intelligent battery management deliver 87% more power than with conventional batteries. “Electronic Cell Protection” (ECP) protects the battery from overload, overheating and total discharge.
- > ProCORE Li-Ion battery with high-power cells, charge status indicator and “Electronic Cell Protection” (ECP). ECP protects against overload, overheating and total discharge.
- > Ideally equipped for every form of use. Mobile working with the L-BOXX system.

Supplied

- | | | |
|----------------------------|--|----------------------------------|
| ✓ 1 handle | ✓ 1 depth stop | ✓ 1 x tool cloth |
| ✓ 1 tool case (L-Boxx 136) | ✓ 2 Li-Ion storage battery GBA 28V 5.0 Ah AS (92604346020) | ✓ 1 rapid charger GAL 1880 CV AS |

Technical data

GENERAL TECHNICAL DATA

Battery voltage	18 V
Battery capacity	5 Ah
Battery compatibility	Li-ion / ProCORE Li-ion
Battery interface	18 V AMPShare
Motor	brushless
Speed, no load	0 - 980 rpm
Impacts	0 - 4,350 rpm
Impact energy	2.6 J
Tool Holder	SDS-plus
Hole diameter, concrete	26 mm
Hole diameter, masonry	68 mm
Capacity in steel Ø	13 mm
Capacity in wood Ø	30 mm
Weight without storage battery	3.20 kg

VIBRATION AND NOISE EMISSION VALUES

Sound pressure level LpA	88 dB
Uncertainty of measured value KpA	3 dB
Sound power level LWA	99 dB
Uncertainty of measured value KWA	3 dB
Vibration value 1 ahv 3-way	ah,D 15,2 m/s ²
Vibration value 2 ahv 3-way	ah,D 9,9 m/s ²
Uncertainty of measured value Ka	1,5 m/s ²

Examples of use



Powered by



BOSCH

**Kompatibel mit
AMPSHARE-/ Bosch
Professional 18 V
Akkus.** | Compatible
with AMPSHARE/Bosch

Professional 18 V batteries. | Compatible avec
les batteries 18 V AMPSHARE/Bosch Professional. |
Compatible con baterías AMPSHARE/Bosch
Professional de 18 V. | Compatibile con le batterie
AMPSHARE / Bosch Professional da 18 V.

