

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.



ALKALINE BATTERY


Item No.:	Pcs per pack
3221603	5
2521373	10
3556247	500

TECHNICAL DATA

Type:	LR44 (AG13)
Classification:	Non-rechargeable
Chemical system:	Zn/KOH-H ₂ O/MnO ₂
Nominal voltage:	1.5 V
Weight (approx.)	1.75 g
Capacity:	Item No.: 3221603 100 mAh Item No.: 2521373 140 mAh
Loading:	6.8 kΩ (20 ±2 °C)
Cut-off voltage:	1.2 V
Operating conditions:	-18 to +50 °C +10 to +35 °C (recommended)
Storage conditions:	+10 to +25 °C (max. 30 °C), <60 % RH
Heavy metals:	No added mercury (Hg), Cadmium (Cd), or Lead (Pb)
Compliant to:	(EU) 2023/1542

For performance and safety, observe the operating / storage conditions. Capacity varies depending on the applied load, temperature, and cut-off voltage.

DIMENSIONS (mm)



Dimension	Min.	Max.
Ø	11.25	11.60
H	5.00	5.40

