

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

TM6084 VOLTAGE REDUCER (24/12V)

CE

Item no: 3287425

The product connects a vehicle with a 15 Pole / 24 V/DC socket (ISO 12098) to a 13 Pole / 12 V/DC plug (ISO 11446) on a trailer.



The installation and wiring must only be performed by a professional that is familiar with the applicable standards and regulations.

TECHNICAL DATA

Application

Industry	Commercial vehicles, agricultural machinery, passenger cars
----------	---

Approval

E-mark approval	e24
-----------------	-----

Limitations

Limitations	Only for incandescent lamps and LEDs with a ballast adapter The product must not be used with mechanical flasher relays
-------------	--

Input

Type	Plug
Standard	ISO 12098-2004 (ABS, EBS)
Poles	15
Connection	Clamp hook
Input voltage	24 V/DC



Output

Type	Socket
Standard	ISO 11446-2004
Poles	13
Output voltage	12 V/DC
Output current	0.5 - 2 A (per channel)
Output power	max. 105 W (max. 15 W per channel)
Protection	Over-current protection (10 A); Over-temperature protection; Reverse polarity protection

Others

Material	Brass, PA6
Operating temperature	-25 to +75 °C
Efficiency	50 %
Dimensions (L x W x H)	200 x 80 x 90 mm
Weight	440 g

CONTENTS

Voltage reducer

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*3287425_V1_1124_en_ds 1674089099 I1/O1 en