

Creative Pebble V2



Creative Pebble V2 is a set of 2.0 USB desktop speaker, powered by higher USB-C power and connected to devices through the universal 3.5mm AUX-in cable.

- Powerful 2" Full-range drivers and passive radiator for an impressive audio performance
- Drive it in high gain mode for up to 8W of total power
- 45° elevated drivers that angles at you for personal listening
- Easy access volume controls that are right in front of you
- Powered by USB-C higher power eliminates the need of a wall outlet

¹ With Gain set to "High", using 10W USB C Port or USB C Power Adapter (not included), or
With Gain set to "High", using 5V 2A USB Type-A Power Adapter (not included).

Creative Pebble V2	
Technical Specifications	
Speakers Dimension	116 x 122 x 115 mm / 4.5 x 4.8 x 4.5 inches
Product Weight	• Left Speaker: 0.30 kg / 0.66 lbs • Right Speaker: 0.34 kg / 0.76 lbs
Packaging Weight	• O/Box: 0.88 kg / 1.94 lbs • C/Box: 10 kg / 22 lbs
Packaging Dimension	• O/Box: 239 x 124 x 124 mm / 9.4 x 4.9 x 4.9 inches • C/Box: 655 x 249 x 275 mm / 25.8 x 9.8 x 10.8 inches
Connector type	3.5mm Analogue Stereo Connector, USB C
Molded Cable type	• Line In: 1.2m cable terminated with 3.5mm stereo jack • DC Power: 1.2m cable terminated with USB Type-C • Right to left Speaker: 1.35m molded cable
Color	Black
Power Output	2 x 4W RMS
Total System power	Up to 8W ¹ RMS, Peak Power 16W
System Configuration	2.0 System
Frequency Response	100Hz ~ 17kHz
SNR	75dB
Operating Temperature	0°C to 45°C
Type	2" Full range Speaker Driver with Passive Radiator
Minimum System Requirement	
	• USB power via desktop/ laptop USB ports • For best experience, connect to higher current USB power adapter up to 5V 2A output, or USB C 10W power adapter • Analog audio devices with a 3.5mm stereo output
Package Content	
	• 2 x speakers satellites • 1 USB C to USB-A Converter • 1 Warranty and Technical Support Booklet
Warranty	
	• 1 year Limited Hardware Warranty