

Creative Pebble V3

MINIMALISTIC 2.0 USB-C SPEAKERS WITH *BLUETOOTH*® 5.0



The ever popular Pebble series is now enhanced with new Pebble V3, boasting *Bluetooth* 5.0 and USB digital audio connectivity. In pursuit of audio excellence, Pebble V3 also carries the Clear Dialog audio processing to improve speech intelligibility and vocal clarity.

- *Bluetooth*® 5.0 connectivity with USB audio for digital audio playback
- Powerful 2.25" full-range drivers and passive radiators for enhanced audio experience
- Hear better with Clear Dialog audio processing
- Amplified audio with High Gain Mode through built-in gain switch
- 45° elevated drivers that gives audio a greater dimension

¹ With 10W USB C Port or USB C Power Adapter (not included). Gain set to "High" or with 5V 2A USB Type-A Power Adapter (not included). Gain set to "High"

Creative Pebble V3	
Technical Specifications	
Dimensions	Speakers: 123 x 120 x 118 mm / 4.8 x 4.7 x 4.6 inches
Weight	• Product: 0.73 kg / 1.6 lbs • Left Speaker: 0.31 kg / 0.68 lbs • Right Speaker: 0.36 kg / 0.79 lbs
Packaging Weight	• O/Box: 0.92 kg / 2.03 lbs • C/Box: 7.7 kg / 17.0 lbs
Packaging Dimension	• O/Box: 250 x 130 x 130 mm / 9.8 x 5.1 x 5.1 inches • C/Box: 538 x 278 x 264 mm / 21.2 x 10.9 x 10.4 inches
Connector type	3.5mm Analogue Stereo Socket, USB Type-C
Molded Cable type	• USB Cable (for Audio and Power): 1.2m cable terminated with USB Type-C • Right to left Speaker: 1.35m molded cable
Color	White
Power Output	• 2 x 4W RMS • Total System power: Up to 8W¹ RMS, Peak Power 16W
System Configuration	2.0 System
Frequency Response	100Hz ~ 17kHz
SNR	75dB
Operating Temperature	0°C to 45°C
Speaker Driver	2.25" Full range Speaker Driver with Passive Radiator
Minimum System Requirement	
Windows	• Intel® i3 or AMD® equivalent processor • Intel, AMD or 100% compatible motherboard • Microsoft® Windows 8.1/8.0 32/64 bit, Windows 10 32/64 bit or higher • 1GB RAM, >600 MB of free hard disk space • Available USB Type-C or USB Type-A port
Macintosh	• Macintosh running MacOS 10.12 or higher • 1GB RAM, >600 MB of free hard disk space • Available USB Type-C or USB Type-A port
Package Content	
• 2 x speakers satellites • 1 x USB C to USB-A Converter • 1 x Warranty leaflet • 1 x Quick Start Guide	
Warranty	
• 1 year Limited Hardware Warranty	