

CREATIVE ZEN HYBRID SXFI

Wireless Over-ear Headphones with Super X-Fi® Technology

Creative Zen Hybrid SXFI brings you an unparalleled experience and expanded soundstage with Super X-Fi Spatial Holography, packed in a compact, sleek headphones to bring your listening experience to newer heights.



POWERED BY SUPER X-FI® SPATIAL HOLOGRAPHY - Hear every nuance and detail just as they are meant to be heard, and enjoy your very own full-fledged cinematic audio experience right from the comfort of your headphones

HITTING THE SWEET SPOT – Our powerful custom-tuned 40 mm Neodymium drivers ensure precise highs and lows, while low latency mode keeps your listening experience uninterrupted and smooth. Plus, you can tailor your sound preferences with the EQ module on the Creative app

MATCHING MODES TO YOUR MOOD – With Hybrid ANC, adaptive ANC, or Ambient mode, we let you switch between full noise canceling for complete focus, intelligently blocking unwanted noise, or full awareness of your surroundings

GET READY FOR HYBRID FUN - These headphones deliver the ultimate versatility with wireless or wired connectivity via **Bluetooth®** 5.3 or a 3.5 mm analog cable. Perfect for movies, music, gaming, and beyond

TRAVEL-READY COMFORT, DOWN TO THE DETAILS – With up to 70 hours of playtime (ANC off) or 40 hours (ANC on), built-in mics featuring Environmental Noise Cancellation technology for crisp, clear call quality, plush ear cushions, headbands, and 90° swivel earcups, these headphones are designed for the long haul



Part No. / Description: 51EF1200AA000 / SYS, HEADSET CREATIVE ZEN HYBRID SXFI GY WW

UPC Barcode: 0 54651 19624 7
EAN Barcode: 53 90660 196249
JAN Barcode: 4580181854488
GTIN Pallet: 70054651196246
GTIN Master: 50054651196242
Japan Model#: HS-ZHBSFI-GY

Part No. / Description: 51EF1200AA001 / SYS, HEADSET CREATIVE ZEN HYBRID SXFI BK WW

UPC Barcode: 0 54651 196339
EAN Barcode: 53 90660 196331
JAN Barcode: 4580181854617
GTIN Pallet: 70054651196338
GTIN Master: 50054651196334
Japan Model#: HS-ZHBSFI-BK

CREATIVE ZEN HYBRID SXFI	
Technical Specifications	
Model No	EF1200
Product Color	- Gray - Black
Headphone Drivers	- Size: 40mm Neodymium - Frequency Response: 20Hz ~ 20kHz - Sensitivity: 119dB SPL - Impedance: 32 ohms
Microphones	Type: Omni-directional x 5 4X ANC mic: - Sensitivity @1KHz -34dbV - Mic impedance 2.2kohm 1x voice mic: - Sensitivity @1KHz -32.5dBV - Mic impedance 2.2kohm
Frequency response	100 Hz ~ 10 kHz
Bluetooth Version	Bluetooth® 5.3
Bluetooth Profiles	- A2DP (Wireless Stereo Bluetooth) - AVRCP (Bluetooth Remote Control) - HFP (Hands-free Profile) - HSP (Headset Profile)
Audio Codecs	SBC, AAC
Bluetooth Operating Frequency	2402 MHz ~ 2480 MHz
Wireless Operating Range	Up to 15m
Maximum RF Output Power	3 dBm
Battery Type	1x Lithium-ion Battery, 3.7V, 500mAh
Charging Interface	USB-C (Charging)
Charging Time	2 hour
Playtime¹ (Default)	- Up to 70 Hours (Without ANC / ANC Off) - Up to 40 Hours (With ANC / ANC On)
Operating Temperature	0~45°C
Product Dimensions (L x W x H)	151.22 x 80.65 x 184.22 mm
Accessories Dimension	- USB-C to USB-A Cable: 0.8 m / 2.62 ft 3.5mm Aux Cable: 1.2 m / 3.94 ft
Product Weight (g)	Headphone: 257g
Minimum System Requirement	
	iOS - iPhone / iPads with Bluetooth for wireless audio streaming Android - Phones / Tablets with Bluetooth for wireless audio streaming PC - All PC / Laptop with Bluetooth A2DP and AVRCP - Creative App requires Windows 10/11 Mac - All Apple computers with Bluetooth A2DP and AVRCP
Package Content	
	1 x Creative Zen Hybrid SXFI 1 x USB Type C-to-A Charging cable (0.8 Meter) 1 x Aux 3.5mm cable (1.2 Meter) 1 x QSG/Warranty/Compliance Leaflet
Warranty	
	1-year limited hardware warranty (Outside Europe) 2-year limited hardware warranty (Europe)

¹Actual battery life may vary depending on usage and settings