

CREATIVE OUTLIER GO

Wireless Open-Ear Headphones with Adjustable Fit

Music you can feel and listen to on any adventure or commute, all while maintaining situational awareness around you. The open-ear headphones provide full audio immersion with its custom-tuned 14.2 mm Neodymium drivers, with precise up-down-left-right adjustments for a personalized fit at all times.

A DIFFERENT WAY OF LISTENING - Mimicking the natural curvature of your ear, its ear-hook open-ear design and custom-tuned 14.2 mm Neodymium drivers immerse you in full audio quality while maintaining situational awareness. Further accompanied by low latency mode for an uninterrupted, smooth listening experience

DESIGNED WITH PRECISE UP-DOWN-LEFT-RIGHT ADJUSTMENTS – Creative Outlier Go's adjustable fit ensures a tailored fit to every ear. With an ultra-smooth, soft silicon finish on the ear hooks, enjoy both comfort and adventure rolled into one

GO EVEN FURTHER - With an IPX4 rating, paired with a long battery life of up to 26 hours total playtime with 6 hours per charge, Creative Outlier Go is all ready to stand by you every moment of your day, all day in and day out

GROOVE ON THE GO WITH *BLUETOOTH 5.4* - Enjoy consistent smooth audio streaming with multipoint connectivity, which allows you to connect to two devices simultaneously and elevate your multitasking game

CONVENIENCE AT YOUR FINGERTIPS - Simply tap the earbud to manage music, volume, and calls using intuitive touch controls. Customize your experience further with the Creative app, offering personalized controls tailored to your preferences





Part No. / Description:., 51EF1210AA001 / SYS,HEADSET CREATIVE OUTLIER GO BU WW

UPC Barcode:., 0 54651 196278
EAN Barcode:., 53 90660 196270
JAN Barcode:., 4580181854525
GTIN Pallet:., 70054651196277
GTIN Master:., 50054651196273
Japan Model#:., HS-OTLGO-BU

Part No. / Description:., 51EF1210AA000 / SYS,HEADSET CREATIVE OUTLIER GO WH WW (TBC)

UPC Barcode:., 0 54651 196261
EAN Barcode:., 53 90660 196263
JAN Barcode:., 4580181854518
GTIN Pallet:., 70054651196260
GTIN Master:., 50054651196266
Japan Model#:., HS-OTLGO-WH

CREATIVE OUTLIER GO	
Technical Specifications	
Model Number	• EF1210
Color	• White (TBC) and Blue
Headphone Drivers	• 14.2 mm Neodymium Driver x 2 • Frequency Response: 20–20,000 Hz • Sensitivity (1 kHz / mW): 100.5 dB • Impedance: 32Ω
Microphones	• Type: mic x1 (per earbud) • Sensitivity (1 kHz): -38 dBV/Pa
Bluetooth version	• Bluetooth 5.4
Bluetooth Profiles	• A2DP (Advanced Audio Distribution Profile) • AVRCP (Audio / Video Remote Control Profile) • HFP (Hands-free Profile) • HSP (Handset Profile)
Audio Codecs	• SBC, AAC
Operating Frequency	• 2402 – 2480 MHz
Operating Range	• Up to 10m / 33 ft.
Maximum RF Output Power	• 13 dBm
Voice Assistant Support	• Siri and Google Assistant
Battery	• Earbud (Left and Right): 1 x Lithium-ion 3.7V 60mAh 0.222 Wh • Charging Case: 1 x Lithium-ion 3.7V 600mAh 2.22 Wh
Playtime ¹ (Default)	• Up to 6 Hours Per Charge (ANC Off) • Up to 26 Hours of Total Playtime (ANC Off)
Charging Interface	• USB-C (Charging)
Charging Time	• Up to 2 hours
IP Rating	• IPX4 (Earbuds)
Operating Temperature	• 0–45°C
Dimensions (L x W x H)	• Earbud (Per Side): 54 x 40.34 x 16.63 mm • Charging Case: 103 x 55 x 25.80 mm
USB Cable Length	• 30 cm
Weight	• Earbud (Per Side): 11 g • Charging Case: 56 g
Minimum System Requirement	
	iOS • iPhone / iPads with <i>Bluetooth</i> for wireless audio streaming Android • Phones / Tablets with <i>Bluetooth</i> for wireless audio streaming PC • All PC / Laptop running Windows 10 and 11 with <i>Bluetooth</i> A2DP and AVRCP Mac • All Apple computers with <i>Bluetooth</i> A2DP and AVRCP
Package Content	
	• 1 x True Wireless Earbuds (L and R) • 1 x Charging case • 1 x USB type C charging cable 30cm • 1 x Quick Start Guide/Warranty/Compliance Leaflet
Warranty	
	• 1-year limited hardware warranty (Outside Europe) • 2-year limited hardware warranty (Europe)

¹Actual battery life may vary depending on usage and settings