











Wiring Method

NOTE:

- Operating Temperature:0℃~45℃
- Storage Temperature:-20℃~ 70℃
- Operation humidity:10%~85%
- Storage humidity:10%~85%
- RoHS(EU2015/863) and Reach compliant.
- Note:If the usb c devices with 3.5mm audio port, it may not support
- packing: 1pc/ plain box+label

MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT'Y	REMARK
⑤	Outer mold	BLACK PVC	3	
④	housing	Aluminum gray	3	
③	3.5SP AL SHELL	The Pin Gold Plating, the shell for Nickel Plating	2	
②	TYPE C Male	The Pin Gold Plating, the shell for Nickel Plating	1	
①	Cable	30AWG Enamelled Wire OFC x4C+kevlar,Red/green/red+green/nature Jacket:PVC, black Black Braid OD: 2.7±0.2mm	1	

FN 29212c521

Renkforce

CUSTOMER	CN	BN.		
PRODUCT NAME	Premium USB 3.2 Type C male to 2×3.5mm Female Adapet Aluminum Housing		UNIT	MM

BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	DRAWNBY	CHECKBY	APPOBY	DATE
		NEW	2024/09/03	A1	Jiang	Alvan		2024-09-03