

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

14500 LI-ION RECHARGEABLE BATTERY



Item No.:	Qty.
3313977	1


TECHNICAL DATA

Type:	14500
Classification:	Rechargeable
Chemical system:	Lithium-ion
Nominal voltage:	3.7 V
Capacity	1000 mAh
Charge voltage (max.):	3.7 V
Charging current (max.):	0.5 A
Terminal voltage:	2.75 V
Discharge current (max.)	3 A
Continuous discharge:	1 A
Terminals:	Flat-top
Weight (approx.):	20 g
Operating conditions:	Charge: 0 to +45 °C Discharge: -10 to +60 °C Humidity: <65 % RH
Storage conditions:	-5 to +35 °C, 25 - 75 % RH
Compliant to:	IEC 62133

*For performance and safety, observe the operating / storage conditions.



DIMENSIONS



D:	14.2 mm ±0.15
W:	6.7 mm ±0.1
H:	49.0 mm ±0.3

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing. Copyright 2025 by Conrad Electronic SE.
*3313977_v1_0325_02_dm_ds_en