

BU-P6738

(BNC T-connector: Female, Female, Female)



- The BU-P6738 is a female-female-female BNC T-connector.
- Overall length 1.28" (32.6mm)
- Material:

Body	Nickel-plated brass
Contacts	Gold-plated Beryllium Copper
Insulator	PTFE
- Rating:

Impedance	75 Ohms
Temperature	-50°C to 150°C
- RoHS 3 compliant