



WT 1010M 1 CHANNEL MICRO SOLDERING KIT, 95 W, 230 V

ORDER NO: T0053448699

COMPACT. POWERFUL. VERSATILE.
BOOST YOUR PRODUCTIVITY

Discover the WT 1M Soldering Station, your ultimate productivity partner.

With extremely fast heat-up and recovery times, it handles all tasks effortlessly. No more juggling tools or compromising performance – just reliable versatility and unmatched value. Choose worry-free precision and unstoppable productivity. Choose Weller WT Soldering Stations.

+ KEY FEATURES

> 1 CHANNEL MICRO SOLDERING KIT (95 W)

to cover micro and standard soldering tasks including
WTMP MS Micro pencil with active (cartridge) tip technology

> RTM TIP FAMILY

with 5 seconds heat-up time

> HIGH PRODUCTIVITY

> INTUITIVE USE

thanks to clear menu structure

> REDUCED FOOTPRINT

thanks to stackability

> GRAPHICAL BACKLIT LC-DISPLAY

> HIGH PERFORMANCE AND FUNCTIONALITY

many connectable tools

> HOUSING COVER

useable as storage

> OFF TIME, PROCESS WINDOW,

Lock function, Offset

> STACKABLE UNITS

useable as storage

> CONNECTABLE TO

ZeroSmog Fume Extraction Units

> ESD-SAFE



#PowerfulTogether

weller-tools.com

Weller® is a registered trademark of Apex Brands, Inc. © 2024 | Specifications subject to change without notice.



[More information](#)

SCOPE OF SUPPLY

WT1M Power Unit, 230V
WTMP MS Soldering Iron, 12V
RTM 013 S MS Micro Soldering Tip
WSR 205 Safety Rest with Stop & Go Function

TECHNICAL DATA SOLDERING STATION WT 1010M

Dimensions L x W x H (mm) 150 x 130 x 101
Dimensions L x W x H (inch) 5.91 x 5.12 x 3.98

Fuse 230V (mA) T500

Weight approx. (kg) 1,9

Mains supply voltage (V/Hz)
230 / 50

Power consumption (W) 95

Safety class I, antistatic housing
III, Soldering tool

Temperature range / Tool dependent
°C 50 - 450 / 550

Temperature accuracy °C ± 9 / ± 17

Temperature stability °C ± 2

Subject to technical alterations and amendments.

TECHNICAL DATA SOLDERING IRON WTMP MS

Temperature range °C 100 - 450
Temperature range °F 150 - 950

Power consumption (W) 40 W (55 W)

Mains supply voltage (V/Hz) 12V / AC

Heat-up time (50°C to 350°C) (120°F to 660°F) 5 sec.

Safety rest WSR 205

Tip type series RTM MS

Supply unit WT 1M, WT 2M, WR 3M

Subject to technical alterations and amendments.