



## WT1011M 1 CHANNEL NANO/PICO SOLDERING KIT, 95 W, 230 V

ORDER NO: T0053449699

COMPACT. POWERFUL. VERSATILE.  
BOOST YOUR PRODUCTIVITY

### Discover the WT 1M Soldering Station, your ultimate productivity partner.

With extremely fast heat-up and recovery times, it handles all tasks effortlessly. No more juggling tools or compromising performance – just reliable versatility and unmatched value. Choose worry-free precision and unstoppable productivity. Choose Weller WT Soldering Stations.

## + KEY FEATURES

### > 1 CHANNEL NANO/PICO SOLDERING KIT (95 W)

to cover smallest soldering tasks including WTPP MS Nano/Pico pencil with active (cartridge) tip technology

### > RTP TIP FAMILY

with 3 seconds heat-up time High productivity

### > HIGH PRODUCTIVITY

### > INTUITIVE USE

thanks to clear menu structure

### > REDUCED FOOTPRINT

thanks to stackability

### > GRAPHICAL BACKLIT LC-DISPLAY

### > HIGH PERFORMANCE AND FUNCTIONALITY

many connectable tools

### > HOUSING COVER

useable as storage

### > OFF TIME, PROCESS WINDOW,

Lock function, Offset

### > STACKABLE UNITS

useable as storage

### > CONNECTABLE TO

ZeroSmog Fume Extraction Units

### > ESD-SAFE



#PowerfulTogether

weller-tools.com

Weller® is a registered trademark of Apex Brands, Inc. © 2024 | Specifications subject to change without notice.



More information

### SCOPE OF SUPPLY

WT1M Power Unit, 230V  
WTPP MS Soldering Iron, 40W, 12V  
RTP 004 S MS Nano/Pico Soldering Tip  
WSR 205 Safety Rest with Stop & Go Function

### TECHNICAL DATA SOLDERING STATION WT1M

Dimensions L x W x H (mm) 150 x 130 x 101  
Dimensions L x W x H (inch) 5.91 x 5.12 x 3.98

Fuse 230V (mA) T500

Weight approx. (kg) 1,9

Mains supply voltage (V/Hz)

230 / 50

120 / 60

100 / 50/60

Power consumption (W) 95

Safety class I, antistatic housing

III, Soldering tool

Temperature range / Tool dependent

°C 50 - 450 / 550

Temperature accuracy (°C/°F) ± 9 / ± 17

Temperature stability (°C/°F) ± 2 / ± 4

Subject to technical alterations and amendments.

### TECHNICAL DATA SOLDERING IRON WTPP MS

Temperature range °C 100 - 450

Temperature range °F 150 - 950

Power consumption (W) 40W (55W)

Mains supply voltage (V/Hz) 12V / AC

Heat-up time (50°C to 350°C) (120°F to 660°F) 3 sec.

Safety rest WSR 205

Tip type series RTP MS

Supply unit WT 1M, WT 2M, WR 3M

Subject to technical alterations and amendments.