

# Datasheet

Manufacturer Part No.: T24CA097 ... T24CA100

## Hook-and-Loop Cable-Tie Set 100 pcs.

**Part-No.: T24CA097 ... T24CA100**



These hook-and-loop cable-ties made of polyamide are easy to open and close again. Therefore, they are ideally suited for general bundling tasks and fixations of, for example, objects, cables, sports utensils, plants, curtains, tools and much more. The excellent material properties of polyamide allow a wide range of applications as far as environmental conditions are concerned. The material is dimensionally stable, robust and resistant to many liquids and also UV radiation. The supply set of 10 hook-and-loop cable ties with eyelet content is optimal for any indoor and outdoor applications. The black design can be unrestricted and inconspicuous in many usages.

### Technical data:

Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: black • RoHS compliant, REACH compliant.

| Part-No. | Description                                      | Length | Width | Color | Content  | EAN / GTIN    |
|----------|--------------------------------------------------|--------|-------|-------|----------|---------------|
| T24CA097 | Hook-and-loop cable-ties 250 x 12 mm Set (Black) | 250 mm | 12 mm | Black | 100 pcs. | 4260732287469 |
| T24CA098 | Hook-and-loop cable-ties 300 x 14 mm Set (Black) | 300 mm | 14 mm | Black | 100 pcs. | 4260732287476 |
| T24CA099 | Hook-and-loop cable-ties 350 x 14 mm Set (Black) | 350 mm | 14 mm | Black | 100 pcs. | 4260732287483 |
| T24CA100 | Hook-and-loop cable-ties 400 x 16 mm Set (Black) | 400 mm | 16 mm | Black | 100 pcs. | 4260732287490 |