

Hook-and-Loop Tape Roll Item-No.: 24CA307 ... 24CA312



24CA307



24CA308



24CA309



24CA310



24CA311



24CA312

Hook-and-loop-tape without buckles for flexible use and cutting.

Technical data: Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: black • RoHS compliant, REACH compliant.

Part-No.	Description	Length	Width	Color	Content	EAN / GTIN
24CA307	Hook-and-loop tape 10 m x 1 cm on Roll	10 m	1 cm	Black	10 m	4260732287506
24CA308	Hook-and-loop tape 10 m x 3 cm on Roll	10 m	3 cm	Black	10 m	4260732287513
24CA309	Hook-and-loop tape 5 m x 4 cm on Roll	5 m	4 cm	Black	5 m	4260732287520
24CA310	Hook-and-loop tape 5 m x 5 cm on Roll	5 m	5 cm	Black	5 m	4260732287537
24CA311	Hook-and-loop tape 5 m x 7,5 cm on Roll	5 m	7,5 cm	Black	5 m	4260732287544
24CA312	Hook-and-loop tape 3 m x 10 cm on Roll	3 m	10 cm	Black	3 m	4260732287551