

## Hook-and-Loop Extrastrong Cable-Tie Set Item-No.: 24CA313 ... 24CA19



These hook-and-loop cable-ties made of polyamide are easy to open and close again.

A special hook-and-loop technology enables a significantly higher strength of the hook-and-loop connection compared to standard hook-and-loop cable ties!

Therefore, they are ideally suited for a lot of bundling tasks and fixations of, for example, objects, cables, sports utensils, plants, curtains, tools and much more. The excellent material properties of polyamide allow a wide range of applications as far as environmental conditions are concerned.

The material is dimensionally stable, robust and resistant to many liquids and also UV radiation. The supply set of 10 hook-and-loop cable ties with eyelet content is optimal for any indoor and outdoor applications. The black design can be unrestricted and inconspicuous in many usages.



**Technical data:** Material: Polyamide • Temperature range: -20 ... 85 °C • Melting temperature: >250 °C • Color: black • RoHS compliant, REACH compliant.

Part-No.	Description	Length	Width	Color	Content	EAN / GTIN
24CA313	Extrastrong Hook-and-loop cable-ties 100 x 25 mm Set (Black)	100 mm	25 mm	Black	10 pcs.	4260732287568
24CA314	Extrastrong Hook-and-loop cable-ties 150 x 25 mm Set (Black)	150 mm	25 mm	Black	10 pcs.	4260732287575
24CA315	Extrastrong Hook-and-loop cable-ties 200 x 25 mm Set (Black)	200 mm	25 mm	Black	10 pcs.	4260732287582
24CA316	Extrastrong Hook-and-loop cable-ties 250 x 25 mm Set (Black)	250 mm	25 mm	Black	10 pcs.	4260732287599
24CA317	Extrastrong Hook-and-loop cable-ties 300 x 25 mm Set (Black)	300 mm	25 mm	Black	10 pcs.	4260732287605
24CA318	Extrastrong Hook-and-loop cable-ties 350 x 25 mm Set (Black)	350 mm	25 mm	Black	10 pcs.	4260732287612
24CA319	Extrastrong Hook-and-loop cable-ties 400 x 25 mm Set (Black)	400 mm	25 mm	Black	10 pcs.	4260732287629