

Item No.: 3347292 – Black 50 meter
 3347293 – Black 100 meter
 3368780 – Black 300 meter

Data Sheet

Cable specification				
STYLE		H05RN-F 2x1.0		
Standard		EN50525		
Applications		Medium outdoor cable		
Construction Details:				
Test Item		Unit	2x1.0	
Conductor	Material		Copper	
	Construction		32/0.190±0.01	
	Conductor DC resistance at 20℃ ≤		20℃ ≤19.5Ω/km	
Core Insulation	Material		EPDM	
	Avg. thickness	mm	0.6	
	Min. thickness	mm	0.44	
	Over Diameter	mm	2.5±0.10	
	Surface		Smooth	
	Colors		brown、blue	
lay	filler		NO	
Jacket	Material		CPE	
	Avg. thickness	mm	0.9	
	Min. thickness	mm	0.67	
	Over Diameter	mm	6.9±0.4	
	Surface		Smooth	
	Colors		BLACK	
Marking			◁VDE▷ 40015999 H05RN-F 300/500V 2×1.0mm2 RIFENG	