








* SUBJECT TO CHANGE WITHOUT NOTICE



NOTES:

ELECTRICAL:

1. VOLTAGE RATING: 125 VAC RMS
2. CURRENT RATING: 1.5AMP
3. CONTACT RESISTANCE: 20MΩ MAX
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @500 VDC
5. DIELECTRIC STRENGTH: 750 VAC RMS 60Hz, 1MIN

ENVIRONMENTAL:

1. STORAGE: -40° TO +85°
2. OPERATION: 0° TO 70°

MECHANICAL:

1. HOUSING MATERIAL: PC
2. PCB MATERIAL: FR-4 T=1.6mm
3. CONTACT MATERIAL: PHOSPHOR BRONZE
STAMP PIN 0.30mm
4. IDC LIFE: 200 TIMES MIN
5. WIRE: AWG 23-26
6. Nut material: Plastic

DRAWN	CHK'D	Ku Chou	APP'D	KUNG	UNIT	MM	TOLERANCE	.x xx xxx xxxx	±0.20 ±0.10 ±0.05 ±0.03	ANGULA ±1°	TITLE	CAT6A SHIELDED PLUG, TOOLTEST TYPE.		SHEET
											PART NO.	DWG NO.	VERSION	
		Enly Suen			SCALE	1:1					2542 01	RJ-S06A-88-ST	A	