












* SUBJECT TO CHANGE WITHOUT NOTICE



NOTES:

ELECTRICAL:

1. VOLTAGE RATING: 125 VAC RMS
2. CURRENT RATING: 1.5 AMP
3. CONTACT RESISTANCE: 20MΩ MAX
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @500 VDC
5. DIELECTRIC STRENGTH: 750 VAC RMS 60Hz, 1MIN

ENVIRONMENTAL:

1. STORAGE: -40 °TO +85 °
2. OPERATION: 0 °TO 70 °

MECHANICAL:

1. HOUSING MATERIAL: ZINC ALLOY
2. IDC MATERIAL: PC
3. PCB MATERIAL: FR-4 T=1.6mm
4. CONTACT MATERIAL: PHOSPHOR BRONZE
STAMP PIN 0.30mm
5. IDC LIFE: 200 TIMES MIN
6. WIRE: AWG 22-26

DRAWN		Ku Chou		APP'D		KUNG		UNIT		MM		TOLERANCE		°		Lumberg Connect GmbH		TITLE		CAT.6A SHIELDED PLUG TOOLSET TYPE , WITH BOOT.		SHEET	
CHK'D		Enly Suen						SCALE	1:1			.x xx xxx xxxx ANGULA	±0.20 ±0.10 ±0.05 ±0.03 ±1°					PART NO.	2542 02	DWG NO.	RJ-S06A-88-BT	VERSION	A