






* SUBJECT TO CHANGE WITHOUT NOTICE



NOTES:

ELECTRICAL:

1. VOLTAGE RATING: 125 VAC RMS
2. CURRENT RATING: 1.5AMP
3. CONTACT RESISTANCE: 20MΩ MAX
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @500 VDC
5. DIELECTRIC STRENGTH: 750 VAC RMS 60Hz, 1MIN

ENVIRONMENTAL:

1. STORAGE: -40° TO +85°
2. OPERATION: 0° TO 70°

MECHANICAL:

1. HOUSING MATERIAL: ABS
2. PCB MATERIAL: FR-4 T=1.0mm
3. CONTACT MATERIAL: PHOSPHOR BRONZE
STAMP PIN T=0.30mm
4. RJ45 JACK ; IFE: 750 TIMES MIN
5. SHIELD MATERIAL: STAINLESS STEEL,
T=0.2mm

REV.	DESCRIPTION	APPROVED BY	DATE	ECN NO.
A	RELEASE	KUNG	2019.12.11	
B				
C				

DRAWN	Ku Chou	APP'D	KUNG	UNIT	MM	TOLERANCE	 X XX XXX XXXX ANGULA		Lumberg Connect GmbH			TITLE	CAT6A SHIELDED INLINE COUPLER.		SHEET 
	CHK'D								Enly Suen	PART NO.	DWG NO.	RJ-S06A-8F8F	VERSION A		