



LaserCube green

Extremely practical compact green line laser for quick alignment work on the ground and on walls

This practical line laser is ideal for rapid alignment work on the floor and on the wall. The device can be easily aligned using vertical and horizontal vials and can also be used as a laser spirit level. Special pins ensure secure, damage-free fixing. Use is convenient thanks to the very bright, green laser and the compact casing, which is mainly made of recycled plastic, contributing greatly to sustainability.

- Sustainable design: large proportion of the housing is made from recycled plastic
- Accurate horizontal and vertical alignment of objects
- Suitable for use on floors and walls
- Safe attachment with special pins without damaging surfaces such as finishing coats, carpets, wood, veneered surfaces etc.
- Good visibility through green laser technology
- Bubble levels for adjustment
- Powerful lithium-ion battery with long operating time
- Extremely easy to use due to compact design



TECHNICAL DATA

Vial Accuracy	± 0.5 mm / m
Accuracy	± 1 mm / m
Levelling	manual
Visibility (Typical)*	10 m
Laser Wavelength	515 nm
Laser Class	2 / < 1 mW (EN 60825-1:2014/ A11:2021 / EN 50689:2021)
Power Supply	Li-ion battery pack 3.7V / 0.7Ah
Operating Time	approx. 7 hours
Operating Conditions	0°C ... 40°C, max. humidity 80% rH, no condensation, max. working altitude 4000 m above sea level
Storage Conditions	-10°C ... 70°C, max. humidity 85% rH
Dimensions (W x H x D)	44 mm x 37.5 mm x 44 mm
Weight	54 g (incl. batteries)



SCOPE OF DELIVERY



Item No. 081.109E

GTIN (EAN) 4021563731862

SU 5