



SmartCross-Laser GX Plus Set


Compact green cross-line laser with excellent visibility, 1/4" thread and multi-function bracket - recycled material is used for sustainability

This cross-line laser projects a highly visible green laser cross for precise horizontal and vertical alignment of objects. It also has a manual slope function for easy creation of gradients. The PocketWallHolder included in the scope of delivery is a multi-functional, height-adjustable, magnetic bracket for attaching the laser to walls, metal items and tripods with a 1/4" or 5/8" thread. The laser can also be used for outdoor applications and alignment work at long distances with the integrated hand-held receiver mode. The housing of the laser is made from a large proportion of recycled plastic and makes a valuable contribution to sustainability.

- Sustainable design: large proportion of the housing is made from recycled plastic
- Accurate horizontal and vertical alignment of objects
- Good visibility through green laser technology
- Height-adjustable, magnetic, multi-function bracket with 1/4" and 5/8" thread for attaching to walls, metal items and tripods
- Easy alignment of slopes with manual tilt function
- Integrated hand-held receiver mode for outdoor applications
- Visual signals indicate when the device is outside its self-levelling range
- Pendulum restraint for safe transport

TECHNICAL DATA

Self-Levelling Range	± 4°
Accuracy	± 0.3 mm / m
Levelling	automatic
Visibility (Typical)*	40 m
Laser Wavelength	515 nm
Laser Class	2 / < 1 mW (EN 60825-1:2014/ A11:2021 / EN 50689:2021)
Power Supply	2 x 1.5V LR6 (AA)
Operating Time	approx. 6 hours
Operating Conditions	-10°C ... 50°C, max. humidity 80% rH, no condensation, max. working altitude 4000 m above sea level
Storage Conditions	-20°C ... 70°C, max. humidity 85% rH
Dimensions (W x H x D)	84 mm x 76 mm x 62 mm
Weight	276 g (incl. battery)



Optional: RangeXtender G 30
Artikel-Nr.: 033.26E

max.
30 m



AUTOMATIC LEVEL



SCOPE OF DELIVERY



Item No. 036.732E

GTIN (EAN) 4021563731800

SU 2