

Product information

82 02 250

KNIPEX TwinGrip

Front and side gripping plier



- Gripping, tightening and loosening screws with worn heads and threads
- Unique combination: Front grip and side grip function, box joint, push button adjustment
- High-grip front jaw with robust teeth and high gear ratio at the tip of the mouth
- Powerfully grips even large, very tight and deep-seated components with A/F 5 – 27 mm
- With comfort handles: consisting of three ergonomic components for optimized handling and equipped with two KNIPEXtend interfaces for extensions
- Very slim pliers: work even in confined spaces, with slim turning zone for fast screwing
- Large front and side gripping capacities: for diameters and width across flats 5 – 27 mm
- Reliable, frontal gripping of flat workpieces up to 10 mm thanks to three-point system
- Seven-way adjustable slip joint with push button adjustment for precise adjustment of gripping capacity
- Pinch stop reduces the risk of crushed fingers
- Durable and resilient thanks to robust box joint

General

Article No.	82 02 250
EAN	4003773089384
pliers	grey atramentized
head	polished
handles	with comfort handles
Weight	393 g
Dimensions	257 x 50 x 21 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

adjustment positions	7
Capacities for pipes (diameter)	Ø 1/16 – 13/64 Inch
Capacities for pipes (diameter)	Ø 5 – 27 mm
Capacities for nuts	5 – 27 mm
Capacities for nuts	13/64 – 1/16 Inch

technical change and errors excepted

