

## EV PORTABLE CHARGER

Max 11KW - 3 Phase - Type 2



Adjustable Rated Current from 8A to 16A

Delayed start up timer function

### SPECIFICATIONS:

Power Phase:	3-Phase	Main Material:	Thermo Plastic/Silicon Rubber / CopperAlloy
Model No.:	P3P6MT2	Cable Spec.:	5*2.5mm <sup>2</sup> +2*0.5mm <sup>2</sup>
Working Voltage:	380V~450V	Cable Length:	6m
Rated Current:	8-10-13-16A	IP-class:	65/54
Insulation Resistance:	>1000MΩ	Fire rating:	UL94 V-0
Resistance Voltage:	2000V	Operating Temperature:	(-30°C ~ 50°C)
Contact resistance:	less than 0.5mΩ	Net Weight:	3.0 kg
Insertion and Extraction Force	80N<F<100N		

**DISTRIBUTED BY:**

**BLP EV SYSTEMS APS - EDITHS ALLÉ 8, 5250 ODENSE SV, DENMARK**