



Power
adjustable



Intelligent
appointment



plug and
play



safety
protection



superior
performance



strong and
sturdy



low-temperature
work



low energy
consumption

Model	ES16AM25
Rated voltage	230VAC+15% 1ph
Rated current	8/10/13/16A
Grid frequency	50/60 Hz
IP protection class	IP65
Operating temperature	-30℃ ~ +50℃
Storage temperature	-40℃ ~ +85℃
Humidity	Up to 75%, maximum value at 40℃
Altitude	2000 m
Protection	Over-voltage protection/Under-voltage protection/ Over-current protection/Short-circuit protection/ Ungrounded protection/Over-temperature protection/ A+6mA Leakage protectionlph
Operating instruction	LED & Display
Dimensions	200(L)x100(W)x55(H)mm
Total length	5m
Weight	1.75 kg
Connector Type	T2

Standards

EN 62752:2016/EN IEC 61851-1:2019/
IEC 62196-1:2014/IEC 62196-2:2016