



DATASHEET

Soldering iron

Item No. 3358947

Overview



Technical data

Operating voltage	230 V
Power (max.)	70 W
Grounding	yes
Plug type	5-pin
Temperature range	max. 160 to 480 °C
Tip size (Ø x L)	5.5 x 150 mm
Product Dimensions (Ø x L)	19 x 220 mm
Weight	0.09 kg
Soldering Iron cable length	1.1 m
Operating temperature	-0 to +70 °C
Operating humidity	5 ~ 95% RH
Storage temperature	0 to +60 °C
Storage humidity	5 ~ 70% RH
Spare tips	Item 3358948 and 3358949