Part Number : 1201000002
Product Description : Micro-Change (M12) Field Attachable Connector, PROFIBUS Shielded, Straight Male
Series Number : 120100
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : BA5S06-32



Documents & Resources

Drawings

1201000002_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per ED/01/2018 (15 January 2018)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120100
Description	Micro-Change (M12) Field Attachable Connector, PROFIBUS Shielded, Straight Male
IP Rating	IP67
Product Name	Micro-Change (M12),PROFIBUS
Type	Field Attachable Connector
UPC	78678850052

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Reverse
Material - Connector Body	N/A
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Silver
Net Weight	48.534/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size (AWG)	22