

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1064152005](#)
Status: **Active**
Overview: [Optical Connectivity](#)
Description: iPASS+™ High Density AOC Assembly (iPass+-to-iPass+), Multimode, 50/125µm, Cable Diameter 3.00mm, Cable Length 5.00m

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Fiber Optic Assemblies
Series	106415
Boot Type	N/A
Connector to Connector	iPass+™-to-iPass+™
Mode	Multimode
Overview	Optical Connectivity
Product Name	AOC, iPass+™
UPC	887191172804
Physical	
Cable Length	5.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm
Single Ended	No
Wire/Cable Type	Fiber Optic, Round
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-106415-2001



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
Need more information on product environmental compliance?	
Email productcompliance@molex.com	
Please visit the Contact Us section for any non-product compliance questions.	
China ROHS	Not Reviewed
ELV	Not Reviewed

Search Parts in this Series 106415 Series
Mates With External iPass+ Integrated Connector 76866 , Internal iPass+ Integrated Connector 76867
Use With Mini SAS HD 2.1 4X Cable Assembly 111068 , 111077 , Internal Cable Assemblies 100190

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION