



**Part Number :** [2175001121](#)  
**Product Description :** Pre-Crimped Lead  
Micro-Lock Plus 2.0 Female-to-Micro-Lock  
Plus 2.0 Female, Tin (Sn) Plating, 75.00mm  
Length, 22 AWG, Black  
**Series Number :** 217500  
**Status :** Active  
**Product Category :** Power and Signal Cable  
Assemblies



Documents & Resources

Drawings  
[2175001121\\_sd.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                    |
| REACH SVHC         | Not Contained per D(2024)6225-DC (07 Nov 2024)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

|                        |                                                                                                                            |
|------------------------|----------------------------------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                                                     |
| Category               | Power and Signal Cable Assemblies                                                                                          |
| Series                 | 217500                                                                                                                     |
| Description            | Pre-Crimped Lead Micro-Lock Plus 2.0 Female-to-Micro-Lock Plus 2.0 Female, Tin (Sn) Plating, 75.00mm Length, 22 AWG, Black |
| Application            | Signal, Wire-to-Board                                                                                                      |
| Assembly Configuration | Pre-crimped Lead Only                                                                                                      |
| Connector to Connector | Micro-Lock Plus Both Ends                                                                                                  |
| Product Name           | Micro-Lock Plus                                                                                                            |
| UPC                    | 195842649583                                                                                                               |

### Electrical

|                   |                  |
|-------------------|------------------|
| Voltage - Maximum | 250V AC (RMS)/DC |
|-------------------|------------------|

### Physical

|                                |                      |
|--------------------------------|----------------------|
| Cable Length                   | 75.00mm              |
| Circuits (Loaded)              | 1                    |
| Circuits (maximum)             | 1                    |
| Color - Resin                  | Black                |
| Gender                         | Female-Female        |
| Material - Metal               | Copper Alloy         |
| Material - Plating Mating      | Tin                  |
| Material - Plating Termination | Tin                  |
| Material - Resin               | PVC                  |
| Net Weight                     | 0.431/g              |
| Number of Rows                 | 1                    |
| Packaging Type                 | Bag                  |
| Single Ended                   | No                   |
| Termination Interface Style    | Crimp or Compression |
| Wire/Cable Type                | UL 10002             |
| Wire Size (AWG)                | 22                   |

---

---

This document was generated on Feb 26, 2025