




Part Number : [2153262102](#)
Product Description : Mini-Fit Jr. Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, Gold (Au) Plating, 10 Circuits, Black
Series Number : 215326
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents & Resources

Drawings
[2153262102_sd.pdf](#)

3D Models and Design Files
[2153262102_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Melamine per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	215326
Description	Mini-Fit Jr. Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, Gold (Au) Plating, 10 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Mini-Fit Jr.-to-Pigtail
Product Name	Mini-Fit Jr.
Type	Discrete Wire Assembly
UPC	193264590223

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Cable Length	300.00mm
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	70.945/g
Number of Rows	2

Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	4.20mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1015
Wire Insulation Diameter	1.80-3.10mm
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Fit BMI Right-Angle Dual Row Headers	<u>42404</u>
Mini-Fit BMI Vertical Dual Row Headers	<u>42440</u>
Mini-Fit BMI Right-Angle Dual Row Headers	<u>43810</u>
Mini-Fit BMI Vertical Dual Row Headers	<u>44068</u>
Mini-Fit Jr. Dual Row Test Plugs	<u>44281</u>
Mini-Fit Jr. Plug Housings	<u>5559</u>
Mini-Fit Jr. Vertical Headers	<u>5566</u>
Mini-Fit Jr. Right-Angle Headers	<u>5569</u>
Mini-Fit Jr. Dual Row Headers	<u>87427</u>