



Part Number : [192050004](#)
Product Description : VersaKrimp Parallel
Splice for 8 AWG Wire
Series Number : 19205
Status : Active
Product Category : Splices
Engineering Number : D-355



Documents & Resources

Drawings
[192050004_sd.pdf](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Splices
Series	19205
Description	VersaKrimp Parallel Splice for 8 AWG Wire
Product Name	Parallel,VersaKrimp
UPC	800755060843

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.887/g
Packaging Type	Bag
Wire Size (AWG)	8

Application Tooling

Global

Description	Part Number
-------------	-------------

Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900001</u>
Manual Tool for Crimping Non-insulated 8 AWG thru 4/0 Terminals	<u>192940008</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
RHT1080 Hand Crimp Tool	<u>640034400</u>
Square "DIN" style dies for 8 AWG	<u>640037670</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640074400</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>