

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1060530000

Status:

Active

Overview:

Optical Connectivity Solutions

Description:

FC Connector, Multimode, 127µm Ferrule, 3.00mm Cable Diameter, Metal Coupling Nut, Black Boot



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Fiber Optic Connectors
Series	106053
Cable Size	3.00mm
Comments	Dust Cap Included But Not Shown, Dust Cap Included But Not Shown
Material - Housing	PBT
Mode	Multimode
Overview	Optical Connectivity Solutions
Product Name	FC
UPC	822350267205
Wire/Cable Type	Simplex
Physical	
Alignment Sleeve	N/A
Angled Physical Contact (APC)	No
Boot Color	Black
Boot Type	Straight
Color - Resin	METAL
Ferrule Hole Size	127µm
Ferrule Material	Zirconia PC
Gender	Plug
Mounting Style	Adhesive
Net Weight	8.285/g
Ports	1
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	860530000
Reference - Drawing Numbers	
Sales Drawing	SD-106053-YYY0

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - ED/88/2018 (15 January 2019)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

106053 Series

Mates With

106152 FC Adapter, Ceramic Alignment Sleeve, 106156 FC Adapter, Metal Alignment Sleeve

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION