




Part Number : 479502011
Product Description : 2.4GHz / 5GHz Wi-Fi Stand Alone Antenna, 16.00mm Width, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Series Number : 47950
Status : New Business Not Supported
Product Category : Antennas



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 2-Methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Antennas
Series	47950
Description	2.4GHz / 5GHz Wi-Fi Stand Alone Antenna, 16.00mm Width, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	2.4GHz SMD Stand Alone
Protocol	BLE, BT, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Wi-Fi Antenna
UPC	884982682054

Electrical

Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5900
Band#2 F_Start (MHz)	4800
Electrical Connectivity	Cable
Peak Gain (dBi)	2.6 @ 2.4 GHz, 4.4 @ 5 GHz
Return Loss - S11 (dB)	< -10, < -9
Total Efficiency	>75% @ 5 GHz, >80% @ 2.4 GHz

Physical

Cable Length	200.00mm
Length	35.90mm
Mounting Style	Adhesive
Net Weight	0.960/g
Packaging Type	Tray
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm

Width	15.90mm
-------	---------

This document was generated on Feb 28, 2025