



Part Number : [2153131033](#)
Product Description : Mizu-P25 Male-to-Pigtail
Off-the-Shelf (OTS) Cable Assembly, 2.50mm
Pitch, Waterproof, Single Row, 600.00mm
Length, Tin (Sn) Plating, 3 Circuits, Black
Series Number : 215313
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[2153131033_sd.pdf](#)

3D Models and Design Files
[2153131033_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	215313
Description	Mizu-P25 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.50mm Pitch, Waterproof, Single Row, 600.00mm Length, Tin (Sn) Plating, 3 Circuits, Black
Application	Signal, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Mizu-P25-to-Pigtail
Product Name	Mizu-P25 Waterproof
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264682713

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	125V

Physical

Cable Length	600.00mm
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Resin	Polyester
Net Weight	13.411/g
Number of Rows	1

Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	PVC
Wire Insulation Diameter	1.40-1.90mm
Wire Size (AWG)	20, 22

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mizu-P25 Waterproof Receptacle Housings	<u>52213</u>