

10

9

8

7

6

5



4

3

2

1

MATERIAL NUMBER	ALTERNATE NUMBER	STUD SIZE	PACKAGING
191930143	D-350-06	.146	LOOSE PIECE
191930146	D-350-08	.173	
191930149	D-350-10	.198	
191930152	D-350-14	.265	
191930157	D-350-56	.328	
191930145	D-350-06T	.146	TAPE PARTS
191930148	D-350-08T	.173	
191930151	D-350-10T	.198	
191930155	D-350-14T	.265	
191930158	D-350-56T	.328	



1. MATERIAL: TERMINAL: COPPER
.050 THICK.
PLATING: ELECTRO TIN
2. ALL DIMENSIONS = INCHES / MM

CUSTOMER DRAWING

DIMENSIONS SHOWN (METRIC) INCH			REVISE ONLY ON CAD SYSTEM			
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°			TITLE RING TONGUE TERMINAL #8 AWG			
			molex ETC INC. PINELLAS PARK, FLA. 33781 U.S.A.		SHEET NO. 1 OF 1	DATE 01/01/23
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			PART NO. SEE TABLE		DRWG. NO. SD-19193-016	
DRWG. BY EDB	CHK'D. BY HEB	SCALE NO: NE	FILE NAME SD19193016 DGN	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX-ETC INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		DIV. ET
APP'D. BY RWD					SIZE B	