



Datasheet – TRU Components

Item no.: 3365404



Voltmeter

1. Technical Parameters:

- Display colour: Red
- Display mode: Four 0.36 LED digital tube
- Update rate: About 500 ms/time
- Open size: 45 x 26mm
- Physical size: 48 x 29 x 22 mm (L x W x H)
- Input range: 3.5-30 V
- Power supply: Need the power supply
- Lead wire length: 14 cm
- Measurement range: DC 0-33.00 V
- Operation temperature: -10 to 65 °C
- Measurement accuracy: $\pm (0.3\% + 2 \text{ Digit})$
- Weight: 14g

Red wire (VCC): Power Supply ++(4.5-30 V) Yellow wire (VIN): Measure Voltage Black wire (GND): Power Supply -, Measure Voltage-

2. Dimension drawing

