



**Part Number :** [2174711115](#)  
**Product Description :** Pre-Crimped Lead Ultra-Fit Female-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 18 AWG, Black  
**Series Number :** 217471  
**Status :** Active  
**Product Category :** Power and Signal Cable Assemblies



## Documents & Resources

**Drawings**  
[2174711115\\_sd.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                       |
|--------------------|---------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                          |
| China RoHS         |  |
| EU ELV             | Not Relevant                                                                          |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21                                                    |
| REACH SVHC         | Not Contained per D(2024)6225-DC (07 Nov 2024)                                        |
| EU RoHS            | Compliant per EU 2015/863                                                             |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

|                        |                                                                                                |
|------------------------|------------------------------------------------------------------------------------------------|
| Status                 | Active                                                                                         |
| Category               | Power and Signal Cable Assemblies                                                              |
| Series                 | 217471                                                                                         |
| Description            | Pre-Crimped Lead Ultra-Fit Female-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 18 AWG, Black |
| Application            | Power, Wire-to-Board                                                                           |
| Assembly Configuration | Pre-crimped Lead Only                                                                          |
| Connector to Connector | Ultra-Fit Crimp Terminals                                                                      |
| Keyword                | Pre-Crimped Leads                                                                              |
| Product Name           | Ultra-Fit                                                                                      |
| UPC                    | 195842069794                                                                                   |

### Electrical

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 12.0A            |
| Voltage - Maximum             | 600V AC (RMS)/DC |

### Physical

|                             |                          |
|-----------------------------|--------------------------|
| Cable Length                | 450.00mm                 |
| Circuits (Loaded)           | 1                        |
| Circuits (maximum)          | 1                        |
| Color - Resin               | Black                    |
| Gender                      | Female-Pigtail           |
| Material - Metal            | High Conductivity Copper |
| Material - Plating Mating   | Tin                      |
| Net Weight                  | 4.283/g                  |
| Packaging Type              | Bag                      |
| Single Ended                | Yes                      |
| Termination Interface Style | Crimp or Compression     |
| Wire/Cable Type             | UL 1061                  |
| Wire Insulation Diameter    | 2.03-2.39mm              |
| Wire Size (AWG)             | 18                       |

---

---

This document was generated on Feb 26, 2025