



Part Number : [2175011105](#)
Product Description : Pre-Crimped Lead
Micro-Lock Plus 2.0 Female-to-Pigtail, Tin (Sn)
Plating, 450.00mm Length, 26 AWG, Black
Series Number : 217501
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[2175011105_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	217501
Description	Pre-Crimped Lead Micro-Lock Plus 2.0 Female-to-Pigtail, Tin (Sn) Plating, 450.00mm Length, 26 AWG, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Lock Plus Crimp Terminal
Product Name	Micro-Lock Plus
UPC	195842650725

Electrical

Voltage - Maximum	250V AC (RMS)/DC
-------------------	------------------

Physical

Cable Length	450.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	PVC
Net Weight	1.096/g
Number of Rows	1
Packaging Type	Bag
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 10002
Wire Size (AWG)	26

This document was generated on Feb 26, 2025