



Part Number : [797582037](#)
Product Description : Pre-Crimped Lead
Mega-Fit Female-to-Mega-Fit Female, Gold
(Au) Plating, 150.00mm Length, 16 AWG, Black
Series Number : 79758
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[797582037_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead Mega-Fit Female-to-Mega-Fit Female, Gold (Au) Plating, 150.00mm Length, 16 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mega-Fit Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	Mega-Fit
UPC	889056818209

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Net Weight	4.104/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1015
Wire Size (AWG)	16

Use with Part(s)

Description	Part Number
-------------	-------------

Mega-Fit Receptacle Housing, Dual Row, 2 Circuit, Glow-Wire Capable, Bag	<u>1700010102</u>
Mega-Fit Receptacle Housing, Dual Row, 4 Circuit, Glow-Wire Capable, Bag	<u>1700010104</u>
Mega-Fit Receptacle Housing, Dual Row, 6 Circuit, Glow-Wire Capable, Bag	<u>1700010106</u>
Mega-Fit Receptacle Housing, Dual Row, 8 Circuit, Glow-Wire Capable, Bag	<u>1700010108</u>
Mega-Fit Receptacle Housing, Dual Row, 10 Circuit, Glow-Wire Capable, Bag	<u>1700010110</u>
Mega-Fit Receptacle Housing, Dual Row, 12 Circuit, Glow-Wire Capable, Bag	<u>1700010112</u>
Mega-Fit Receptacle Housing, Dual Row, 2 Circuit, UL 94 V-0, Bag	<u>1716920102</u>
Mega-Fit Receptacle Housing, Dual Row, 4 Circuit, UL 94 V-0, Bag	<u>1716920104</u>
Mega-Fit Receptacle Housing, Dual Row, 6 Circuit, UL 94 V-0, Bag	<u>1716920106</u>
Mega-Fit Receptacle Housing, Dual Row, 8 Circuit, UL 94 V-0, Bag	<u>1716920108</u>
Mega-Fit Receptacle Housing, Dual Row, 10 Circuit, UL 94 V-0, Bag	<u>1716920110</u>
Mega-Fit Receptacle Housing, Dual Row, 12 Circuit, UL 94 V-0, Bag	<u>1716920112</u>