



Part Number : [797582055](#)
Product Description : Pre-Crimped Lead
ValuSeal Male-to-ValuSeal Male, Tin (Sn)
Plating, 150.00mm Length, 18 AWG, Black
Series Number : 79758
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[797582055_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	79758
Description	Pre-Crimped Lead ValuSeal Male-to-ValuSeal Male, Tin (Sn) Plating, 150.00mm Length, 18 AWG, Black
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	ValuSeal Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	ValuSeal
UPC	191128038713

Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Male-Male
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	2.009/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1007
Wire Insulation Diameter	2.00mm
Wire Size (AWG)	18