



Part Number : [191640047](#)
Product Description : Perma-Seal Female
Quick Disconnect for 16-14 AWG Wire, Tab
Size 6.35 x 0.81mm, Carton
Series Number : 19164
Status : Active
Product Category : Quick Disconnects
Engineering Number : SBB-2141



Documents & Resources

Drawings
[191640047_sd.pdf](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
 - REACH SVHC
 - Low-Halogen

- Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19164
Description	Perma-Seal Female Quick Disconnect for 16-14 AWG Wire, Tab Size 6.35 x 0.81mm, Carton
Product Name	Perma-Seal
Type	Quick Disconnect
UPC	800753113329

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Blue
Gender	Female
Glow-Wire Capable	No
Insulated	Partial
Insulation	NiAc
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.024/g
Orientation	Straight
Packaging Type	Carton
Tab Thickness	0.81mm

Tab Width	6.35mm
Temperature Range - Operating	-55° to +125°C
Wire Insulation Diameter	5.97mm max.
Wire Size (AWG)	14, 16
Wire Size mm ²	1.00-2.50

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Insulkrimp Quick Disconnect Terminals, 22-10 AWG	<u>640010400</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640050400</u>