



Part Number : [190690243](#)
Product Description : Krimptite Ring Tongue
Terminal for 12-10 AWG Wire, Stud Size 3/8"
(M9), Length 26.82mm, Mylar Tape Carrier
Series Number : 19069
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : C-140-38T



Documents & Resources

Drawings
[190690243_sd.pdf](#)

3D Models and Design Files
[190690243_stp.zip](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
 - REACH SVHC
 - Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19069
Description	Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 3/8" (M9), Length 26.82mm, Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Type	Ring
UPC	800753068254

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.989/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	3/8" (M9)
Termination Interface Style	Crimp or Compression

Wire Size (AWG)	10, 12
Wire Size mm ²	4.00-6.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Perishable Tooling Spacers for tape product	<u>190270133</u>
ATP Perishable Tool Kit used in ATP Presses that Process Product on Tape	<u>190270300</u>
Mini-Mac Applicator	<u>638851000</u>