




Ø1.87~2.45	0.55~1.39mm ² (AWG# 16~20, AVS-0.5)	51128-***01 51097-***00	黄銅、錫メッキ材 TIN PLATED BRASS t=0.2	50350-9101	バラ状 LOOSE
Ø2~2.6	0.56~1.29mm ² (AVS-0.5~1.25相当) (CORRESPOND TO AVS-0.5~1.25)	51120-***0*		50350-9001	連鎖状 CHAIN
Ø1.87~2.45	0.55~1.39mm ² (AWG# 16~20)	51128-***01 51097-***00			
Ø2~2.6	0.56~1.29mm ² (AVS-0.5~1.25相当) (CORRESPOND TO AVS-0.5~1.25)	51120-***0*			
被覆外形 INS. RANGE	適用電線範囲 WIRE RANGE	適用ハウジング APPLICABLE HOUSING	材料 MATERIAL	ENG. NO.	端子形状 FORM
GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY	SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
10 UNDER ±0.2		DRAWN BY M. SANO	TITLE 2.5/3.0 WIRE TO BORAD CONN. CRIMP RECEPTACLE		
10 OVER 30 UNDER ±0.25		CHECKED BY M. SANO M. SAK			
30 OVER ±0.3		APPROVED BY M. ENOMOTO	MOLEX INCORPORATED		
ANGULAR ±3 °		MATERIAL NO.			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	SEE CHART	DOCUMENT NO. SD-50350-9*01	SHEET NO. 1 OF 1