



Part Number : [192030094](#)
Product Description : Krimptite Temp-Term
Ring Tongue Terminal for 12-10 AWG Wire,
Stud Size 10 (M5), Mylar Tape Carrier
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals
Engineering Number : C-S-128-10T



Documents & Resources

Drawings
[192030094_sd.pdf](#)

Specifications
[PS-19902-011-001.pdf](#)
[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite,Temp-Terms
Type	Ring
UPC	800753050051

Agency

UL	E32244
----	--------

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1.292/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Size (AWG)	10, 12
Wire Size mm ²	2.70-6.60

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>190270088</u>
Mini-Mac Applicator	<u>638851000</u>